



# HM-430 FLUORESCENT PENETRANT

Technical Data Sheet

## Approvals and conformities

ALLISON ENGINES  
ASME  
BOEING  
EADS  
GE  
ISO 3452-2  
LOCKHEED MARTIN  
QPD-AMS 2644  
SAFRAN

**MANUFACTURER: SHERWIN Inc. (USA) / NDT-Europa (NL)**

## DESCRIPTION / APPLICATION(S):

Type I, method A, Level 3 according AMS 2644 and ISO 3452-2 penetrant designed for detecting surface defects.

**Companion products:** DR-60, DR-62 removers

N120 degreaser / N106A,

D-100, D-106, R60, D-90G developer

## ***DIRECTIONS FOR USE***

These describe the basic process, but they may need to be amended by the user to comply with applicable specifications and/or inspection criteria provided by the contracting agency.

### **Application:**

Apply HM-430 only to clean, dry surfaces by spraying, flowing, brushing or dipping.

1/3

12018-07-31F. Héron

**Dwell-Time:**

A 10 minute dwell time is suggested, although in many cases five minutes will suffice. When particularly tight cracks are suspected, or the part is especially critical, the dwell time may be extended to 30 minutes, or longer.

**Do not soak the part.** To increase sensitivity, as well as conserve material, allow the penetrant to drain from the part surface back into the penetrant tank.

**Removal:**

Use a quick, ambient temperature water wash at tap pressure to rinse HM-430 from the part surface. To avoid washing entrapped penetrant from surface flaws, do not use high water pressures and temperatures, or prolonged washing and scrubbing.

**Drying:**

A recirculating oven set no higher than 80°C is suggested. Leave part in oven just long enough to evaporate surface moisture. Drying is improved by using pressurized air to disperse and remove as much excess water as possible before placing part in oven.

**Developing:**

HM-430 is self-developing. Nevertheless it is recommended to use a developer as listed above.

**Inspection:**

Inspect parts under appropriate UV-A radiation (mini 1000 µW/cm², if possible higher or equal to 1500 µW/cm²) and dimmed visible light (max. 20 lux), it is also possible to use actinic blue light.

**TECHNICAL CHARACTERISTICS**

---

- Very low halogen and sulfur content.
- Compatible with all metals, ceramics, and certain synthetic substances.

Appearance .....	green liquid
Fluorescence .....	green-yellow
Flash point .....	> 93°C
Viscosity .....	18 mm²/s Â±15% at 40°C

**PRECAUTIONS FOR USE AND STORAGE**

---

**Transport / Handling:** Refer to Material Safety Data Sheet (MSDS).

**Storage :** Keep away from moisture

Temperature range: 0°C à 50°C

Keep packaging closed after taking out some of the product.

**This technical data sheet replaces and cancels the previous one.**

The above details have been compiled to the best of our knowledge. They have, however, an indicative value only and we therefore make no warranties and assume no liability in connection with any use of this information, particularly if a third party's rights are affected by the use of our products. The above information has been compiled based upon tests carried out by SOCOMORE. All data is subject to change as Socomore deems appropriate. The data given is not intended to substitute for any testing you must conduct in order to determine the suitability of the product for your particular purposes. Please check your local legislation applicable to the use of this product. Should you need any further information please contact us.